

HAGE3D MEX ONE

TECHNICAL DATA:

MECHANICAL ENGINEERING

Build chamber (XYZ):	400 mm x 600 mm x 440 mm
Heatable build chamber:	up to 100 °C
Heated print bed:	up to 180 °C
Positioning accuracy (XY):	< 0.1 mm
Layer thickness:	from 0.05 mm
Movement speed:	XY~250 mm/s
Air cleaning unit:	Filtration system with active carbon filter and HEPA filter
Safety circuit:	unmanned 24/7 operation

PRINT HEAD

Print head:	Standard-DSD
Nozzle diameter:	0.2 to 1.0 mm (standard: 0.4 mm)
Printing speed:	up to 150 mm/s (depending on geometry and material)
Build-up rate:	up to 200 g/h (depending on geometry and material)
Print temperature:	up to 500 °C

USER CONVENIENCE

Stand-alone printing:	USB/network
Pause printing:	smart 'stop and go' function
Slicing software:	Simplify3D (delivery standard)
Machine control:	HAGE3D industrial control
Operating display:	LED + 7" touchscreen
Filament stock:	runout sensor
Override function:	in real time
User level:	multi-level

INSTALLATION INFORMATION

Power supply:	400 V / 16 A
External dimensions (XYZ):	1270 mm x 1120 mm x 1730 mm
Weight:	approx. 180 kg

MATERIALS:

Wide range of materials: free choice of materials – no manufacturer ties

Printable materials: PC, PC-ABS, PC-FR, PC-CF, PA6, PA6-CF, PA12, PA12-CF, PA12-GF, CoPA, ABS, ASA, ABS-FR, ABS-ESD, TPU, TPC, PETG, PLA, HT-PETG, PCTG, PP, PP-GF, PEKK, PPSU

HIGHLIGHTS:

- ▶ Print bed calibration: automatically by means of multi-point topographic survey
- ▶ Closed-loop technology for accurate step positioning without step losses
- ▶ Glass-fibre reinforced belts in XY direction and trapezoidal spindle in Z direction
- ▶ Component cooling: high-performance, targeted air cooling at up to 4.8 m³/h
- ▶ Heatable built chamber up to 180 °C
- ▶ Filtration system with active carbon filter and HEPA filter for efficient air cleaning of macro, micro and nano particles (VOC) and volatile solvents
- ▶ Real time adjustment of the printing parameters with override function
- ▶ Multi-state user permissions concept, notification via mail inclusive
- ▶ Empty level monitoring for filament stock via mail inclusive

HAGE3D GmbH

Location Obdach: Hauptstraße 52e, 8742 Obdach, Austria

Location Graz: Kratkystraße 2, 8020 Graz, Austria

T: +43 3578 36 412, E: office@hage3d.com, www.hage3d.com

